





The development of new materials, coatings and lubricants is accompanied with all kind of tribology tests. As it is known tribology researches are realize on tribometers Pin on Disk, Block on Disk (Ring), Disk on Disk and Linear reciprocating moving.

There are no many laboratories (University or Institute) with all kind tribometers.

In the last years the universal tribometer are developed in collaboration Serbian Tribology Society and company PRIZMA Kragujevac.

Tribometer
UT '07ES
Disk on Disk
and
Block on Disk
tribometer

The base concept of the Universal tribometer UT'07



Reliable
Wide Load and Speed Ranges
Easy to Operate and Maintain
Modern Measurement Setup
Windows Applicable Software
Low Cost

Normal load: 5-3000 N, $n = 0-4000$ rpm, Disk diameter 10-40 mm.